

OE SERIES

Models

OE750 / OE720

Options

- Adapters
- Sparg parts kit
- Consumable kit
- Sample preparation device
- Floor stand

Wire adapter set



Optical system

- LightWing technology: Multi-CMOS optics in Paschen-Runge mounting and optimized pixel resolution
- Focal length: 400 mm
- Wave length: OE720: 174 - 670* nm / OE750: 119 - 670* nm (*766 nm on request)
- Peak position alignment

Argon supply

- Argon quality: min 4.8 (=99.998 % Ar)
5.0, if analysis of gases is required **(OE750 only)**
- Input pressure: 3 bar

Power supply

- 100 - 240V AC 50/60 Hz
- Power consumption max: 430 W
- Standby mode 45 W (50 W source on)

Readout system

- External PC-Workstation incorporating up-to-date technology with Microsoft® Windows® user interface

Typical applications

- Quality control for process and melt verification: analysis mode / grade identification
- All relevant alloying, residual, treatment, trace and tramp elements with low limits of detection
- Fe: Alloys, cast iron alloys incl. N down to 10 ppm **(OE750 only)**
- Al: Alloys, cast alloys, wrought alloys...
- Cu: Bronze, Brass, Cu-Ni...
- Ni: hasteloy, inconel, monel, incl. N down to 20 ppm
- Ti: Ti pure, Ti.6-4, Ti.8-Mn, incl. gases such as H, O, N **(OE750 only)**
- Mg, Co, Pb, Sn, Zn alloys, solders and more

Solid state source

- Computer controlled parameters
- Frequency: 80 - 1000 Hz
- Voltage: 250 - 500 V
- High energy pre spark (HEPS)

Environmental data

- Temperature range
Storage: -10° to +60°C
In operation: 0° to +40°C
- Humidity range: 10 - 90 % (non-condensing)



Visit www.hitachi-hightech.com/hha for more information.



Hitachi High-Tech Analytical Science

This publication is the copyright of Hitachi High-Tech Analytical Science and provides outline information only, which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or regarded as the representation relating to the products or services concerned. Hitachi High-Tech Analytical Science's policy is one of continued improvement. The company reserves the right to alter, without notice the specification, design or conditions of supply of any product or service.

Hitachi High-Tech Analytical Science acknowledges all trademarks and registrations.

© Hitachi High-Tech Analytical Science, 2021. All rights reserved.